



**SMA-600**  
**MOUNTING PLATE**  
**FOR THE SMART-LIFT 150 AND SMART-LIFT 236**

The SMA-600 mounting plate allows you to attach the Smart-Lift (model SL-150 and SL-236) to a 1½” NPT threaded pipe (compatible with CMA-100 and CMA-110) for suspended ceiling mounting applications.

Unpack carton and check contents:

- |     |                                        |      |                            |
|-----|----------------------------------------|------|----------------------------|
| (1) | Mounting Plate                         | (8)  | 3/8 Washers                |
| (1) | Top Mounting Plate                     | (4)  | 3/8 - 16 Nut               |
| (1) | Bottom Mounting Plate                  | (1)  | 5/16 - 18 Socket Set Screw |
| (4) | 5/16 - 18 Flange Nut                   | (1)  | 5/32 Allen Wrench          |
| (4) | 3/8-16 X 3 1/2” Tap Bolt (SL-236 only) | (10) | 8-32 X 1/2” Screw          |

**CAUTION!!! The overhead support must be capable of supporting five times the weight of the mount and equipment combined. If it cannot, it MUST be reinforced.**

**INSTALLATION INSTRUCTIONS**

1. Attach bottom mounting plate, through mounting plate, to top mounting plate and secure using four 5/16-18 flange nuts on protruding studs of the bottom mounting plate (see picture).
2. Open Smart-Lift (refer to Smart-Lift Instructions).
3. Insert four 3/8- 16 X 3 ½” bolts and washers in holes in top of Smart Lift.
4. Secure mounting plate to Smart Lift using four 3/8 – 16 nuts and washers.
5. *See Smart-Lift installation instructions.*

